

**Plugs and Connectors**

**Plugs**

**Connectors**



**Model 6394**



**Model 6395**



**Model 6396**



**Model 6398**



**Model 6397**




**Model 6332**



**Model 6331**















**Features**

- Use plugs to easily connect to your portable generator.
- Connect to your power inlet box or transfer switch with a connector.



# Plugs and Connectors

## Specifications

Model	6395	6394	6397	6332	6396	6398	6331
UPC	696471063950	696471063943	696471063974	696471063325	696471063967	696471063981	696471063318
Description	Plug	Plug	Plug	Plug	Connector	Connector	Connector
Certification							
Amperage	20	30	30	50	20	30	50
Voltage Rating	125/250 VAC	125 VAC	125/250 VAC	125/250 VAC	125/250 VAC	125/250 VAC	125/250 VAC
Max Generator Size (Watts)	5000	3750	7500	12500	5000	7500	12500
NEMA Configuration	 L14-20	 L5-30	 L14-30	 14-50	 L14-20	 L14-30	 CS6364
Compatible Cord Type (Gauge/Wire)	12/4	10/3	10/4	6/4	12/4	10/4	6/4
Compatible Generac Generators	GP3250, LP3250, XG4000, XP4000	GP15000E, GP17500E, XP4000, XP6500E, XP8000E, XP10000E	GP5500, GP6500E, GP7500E, XG6500, XG7000E, XG8000E, XP6500E, XP8000E	GP15000E, GP17500E, XG10000E, XP10000E	GP3250, LP3250, XG4000, XP4000	GP3250, H3250, LP3250, XG4000, XP4000, GP5500, GP6500E, GP7500E, XG6500, XG7000E, XG8000E, XP6500E, XP8000E	GP15000E, GP17500E, XG10000E, XP10000E
Compatible Generac GenTran Transfer Switches (Model #s)	-	-	-	-	6376, 6378, 6379	6376, 6378, 6379, 6382	6380, 6381, 6335
Compatible Generac GenTran Power Inlet Boxes (Model #s)	-	-	-	-	6337, 6340, 6343, 6346	6337, 6340, 6343, 6346	6338, 6341, 6344, 6347
Package W x H in (mm)	6 x 8 (152 x 203)						
Package Weight lb (kg)	1 (0.5)						
Master Carton UPC	20696471063954	20696471063947	20696471063978	20696471063329	20696471063961	20696471063985	20696471063312
Master Carton Quantity	4						
Master Carton L x W x H in (mm)	9 x 6 x 5 (229 x 152 x 127)						
Master Carton Weight lbs (kg)	4 (2)						