

TX Series Transfer Switch

TXC-100

Automatic Transfer Switch Controller

- Automatic Transfer Switch Controller
- Up to 480 VAC, 50/60 Hz
- Single and Three Phase
- cETLus Recognized Component
- Tested to UL 1008



Image used for illustration purposes only

Codes and Standards

Not all codes and standards apply to all configurations. Contact factory for details.



cETLus Recognized per UL 1008



NFPA 37, 70, 99, 110



NEC 700, 701, 702, 708

Description

Generac's TXC-100 microprocessor based controller provides customers with the flexibility to program a comprehensive group of set points to match the application needs. The controller has 2 programmable inputs and 1 programmable output as standard and is available with an optional expansion board for up to 4 programmable inputs and outputs. The LCD displays real time and historical information with time-stamped events. The integrated plant exerciser can be configured in off, daily, day of week, biweekly, and monthly intervals with user selectable run time. Standard features of the controller include three phase sensing on both sources, phase unbalance, phase reversal, emergency inhibit, and communications.

TX Series Transfer Switch

TXC-100

Automatic Transfer Switch Controller

STANDARD FEATURES

GENERAL

- Graphical LCD-Based Display for Programming, System Diagnostics and Help Menu Display Mimic Diagram with Source Available and Connected LED Indicator
- Time-Stamped Event History Log
- Programmable Exerciser - Daily, Weekly, Bi-Weekly, Monthly
- Methods of Transfer Include: Open with Inphase Transition Only, Time Delay in Neutral Transition, or Inphase with a Default to Time Delay in Neutral Transfer
- Modbus® RTU Communications
- Operating Temperature -4 ° to 158 °F (-20 ° to 70 °C)
- Voltage Agnostic*
- Integrated Anti-condensation Heater Control
- Auxiliary Output Includes: 2WS, SB4T, Fault, and a Programmable Relay Output
- Auxiliary Input Includes: Permissive and Loadshed Inputs (24 VDC)
- Expandable Input/Output Board Module Includes: 4 Relay Outputs and 4 Optically Isolated Inputs
- Front Programmable Control Reduces PPE Needs and Arc Flash Hazard

- Built in Battery Backup - Increases Switch Reliability and Reduces Switch Transition Time to Alternate Source
- Rechargeable Lithium-ion Battery Backup Able to Power the Controller for up to 60 Minutes in the Event of No Source Availability
- Accessible USB Port for Easy Data Downloads, Firmware Updates without Requiring PPE, Reducing the Risk of Arc Flash
- All Amp Nodes Offered with Delayed Transition
- General Alarm Indication
- Heater Programmable through Control for Desired Temperature and Humidity Settings
- Front Accessible Customer Connections and Battery without Arc Flash Exposure
- Auxiliary Generator Battery Backup for Controller

VOLTAGE AND FREQUENCY SENSING

- Three Phase Under and Over Voltage Sensing on Normal and Emergency Sources
- Under and Over Frequency Sensing on Normal and Emergency
- Selectable Settings: Single or Three Phase Voltage
- Sensing on Normal, Emergency and Load 50 or 60 Hz
- Phase Sequence Sensing for Phase Sensitive Loads

PROGRAMMABLE I/O PARAMETERS

Outputs:

- Source 1 – Two Wire Start
- Source 2 – Two Wire Start
- Engine Exercising
- Engine Warmup
- Signal Before Transfer (Elevator Contact)
- General Alarm
- Source 1 Good
- Source 2 Good

Inputs:

- Permissive (Emergency Inhibit)
- Remote Engine Fast Test
- Remote Engine Normal Test
- ATS Timer
- Initiate Demand Response

* 480 V Delta Must be Specified at Time of Ordering for Transformer Kit to be Included

AVAILABLE OPTIONS

- Chicago Code Kit
- 3R Padlockable Cover for Controller (Standard on 3R Enclosure)
- Emergency Inhibit
- Selectable Retransfer
- Manual Generator Retransfer
- Type 1 to 3R Conversion Kit
- Heater Option for Temperature and Humidity Control (Standard on 3R Enclosure)
- Input/Output (I/O) Module
- Current Measurements**
- Power in kW**
- Power Factor**

** When Equipped with Current Transformers